



AFM-P3 Personal Breathalyser

Used with free App for reading and recording results Australian Standard AS3547 Accuracy

- Suitable for personal use only, not recommended for industrial/workplace use
- Electrochemical fuel cell sensor
- Accuracy better than + or - 10%
- Accurate 4 digit decimal LCD display
- Range: 0.000 to 0.400 %BAC
- Power save: auto shut off
- Included: 1 x AAA battery, 6 mouthpieces, protective pouch, user manual
- Calibration recommended every 12 months (no shut out)
- Warranty: 12 months

Compatibility: Bluetooth 4.0 LE

- Requires iOS 7.0 or later. Compatible with iPhone, iPad, and iPod touch.
- Android devices running OS 4.3 or above

PRICES

AFM-P3 \$149 (inc. GST)
 Calibration: \$59

**Plus: \$22.00 including GST postage and handling.
 Conditions apply.**

All prices are per unit and exclusive postage & handling.
 Prices are subject to change without notice.



Very Compact
 7cm x 4cm x 1.5cm



**To Buy On-line
 Scan this Code**



Sydney - Head Office
 PO BOX 7089 Alexandria NSW 2015
 128 O'Riordan Street, Mascot 2020
 Phone: 02 8338 1555 Fax: 02 8338 1688
 Email: nsw@breathalyser.com.au

Perth
 486 Great Eastern Hwy
 Ascot WA 6104
 Phone: 08 9479 3866 Fax: 08 6267 8168
 Email: wa@breathalyser.com.au

Brisbane
 Unit 11, 17-19 University Drive
 Meadowbrook QLD 4131
 PO BOX 6189, Logan Central QLD 4114
 Phone: 07 3200 4944 Fax: 07 3200 4955
 Email: qld@breathalyser.com.au

KEY FEATURES



FUEL CELL SENSOR

Provides accurate and stable readings ranging from 0.000 - 0.400%BAC at an accuracy of +/- five percent.



BLUETOOTH 4.0

Compatible with select iOS and Android.



DUAL MODE

Normal mode - working alone.
App mode - working with app.



APP-ENABLED

Enables the user to track and learn about all his test results, allowing to make a memo and take a photo for personal memory.



LOW BATTERY WARNING

Advises the user to know the correct time for changing the battery.



TEST NUMBER DISPLAY

Helps get on-time calibration service by showing the total number of tests.



Adjustable user menu

Unit, Language, Camera, Sound, Alarm limit, and Healthcare warning message



CALIBRATION REMINDER

Helps get on-time calibration by letting users know the remaining days to next calibration.

SPECIFICATION

Indication of B.A.C.	0.00 ~ 0.40%BAC 0.00 ~ 4.00% 0.00 ~ 2.00mg/l
Accuracy	+/- 0.005%BAC at 0.1%BAC at 25°C +/- 0.05% at 1.0% at 25°C +/- 0.025mg/l at 0.50mg/l at 25°C
Warm up time	Within 15 seconds at 0.50g/l(%) Warm up time may vary depending on the BAC measured.
Sensor	Fuel cell sensor
Power supply	One AAA size alkaline battery
Connectivity	Bluetooth 4.0 LE
Dimensions (WxHxD)	41.5mm x 68mm x 16.9mm
Weight	43g including batteries
Calibration	Every 12 months or After 500 tests
Operating temperature	5 ~ 40°C

* The specifications are subject to change without prior notice for functional improvements.